

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246655

Luminaire Tested: P3AS09R609024DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246655
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609024DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 679.0 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246655

CATALOG NUMBER: P3AS09R609024DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246655

CATALOG NUMBER: P3AS09R609024DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160338
5°	158815
10°	154194
15°	144450
20°	127854
25°	106966
30°	83836
35°	60820
40°	40447
45°	25212
50°	13646
55°	3938
60°	3684
65°	3373
70°	3334
75°	3304
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25212 cd/sqm

TEST NUMBER: P1246655

CATALOG NUMBER: P3AS09R609024DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.9	10.0
10°-20°	176.5	26.0
20°-30°	201.2	29.6
30°-40°	142.7	21.0
40°-50°	64.7	9.5
50°-60°	13.7	2.0
60°-70°	6.6	1.0
70°-80°	4.1	0.6
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.7	65.6
0°-40°	588.4	86.7
0°-60°	666.9	98.2
0°-90°	679.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	679.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	731	
5°	722	68
15°	636	177
25°	442	201
35°	227	143
45°	81	65
55°	10	14
65°	6	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1246655

CATALOG NUMBER: P3AS09R609024DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	731.2
2.5°	728.6
5°	721.5
7.5°	709.2
10°	692.5
12.5°	668.6
15°	636.3
17.5°	595.7
20°	547.9
22.5°	496.3
25°	442.1
27.5°	386.6
30°	331.1
32.5°	278.1
35°	227.2
37.5°	182.0
40°	141.3
42.5°	107.1
45°	81.3
47.5°	60.7
50°	40.0
52.5°	18.7
55°	10.3
57.5°	9.0
60°	8.4
62.5°	7.7
65°	6.5
67.5°	5.8
70°	5.2
72.5°	4.5
75°	3.9
77.5°	3.2
80°	2.6
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)