

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246667

Luminaire Tested: P3AS09R609024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 469.0 lumens
Efficiency: N/A
Efficacy: 42.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246667

CATALOG NUMBER: P3AS09R609024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246667

CATALOG NUMBER: P3AS09R609024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118850
5°	116200
10°	108771
15°	97594
20°	83914
25°	69391
30°	54844
35°	40716
40°	28053
45°	17583
50°	9688
55°	5658
60°	5087
65°	4358
70°	3719
75°	3813
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17583 cd/sqm

TEST NUMBER: P1246667

CATALOG NUMBER: P3AS09R609024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.1	10.5
10°-20°	119.4	25.5
20°-30°	131.0	27.9
30°-40°	95.4	20.3
40°-50°	45.1	9.6
50°-60°	14.8	3.1
60°-70°	8.4	1.8
70°-80°	4.5	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	299.5	63.9
0°-40°	394.9	84.2
0°-60°	454.7	97.0
0°-90°	469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	469.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	542	
5°	528	49
15°	430	119
25°	287	131
35°	152	95
45°	57	45
55°	15	15
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1246667

CATALOG NUMBER: P3AS09R609024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	542.0
2.5°	538.8
5°	527.9
7.5°	511.1
10°	488.5
12.5°	461.5
15°	429.9
17.5°	395.7
20°	359.6
22.5°	322.9
25°	286.8
27.5°	250.7
30°	216.6
32.5°	183.7
35°	152.1
37.5°	123.7
40°	98.0
42.5°	75.4
45°	56.7
47.5°	41.2
50°	28.4
52.5°	18.7
55°	14.8
57.5°	12.9
60°	11.6
62.5°	9.7
65°	8.4
67.5°	7.1
70°	5.8
72.5°	5.2
75°	4.5
77.5°	3.2
80°	2.6
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)