

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246691

Luminaire Tested: P3AS09R659024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 219.0 lumens
Efficiency: N/A
Efficacy: 19.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246691

CATALOG NUMBER: P3AS09R659024DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246691

CATALOG NUMBER: P3AS09R659024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55675
5°	54281
10°	50545
15°	45312
20°	39133
25°	32542
30°	25675
35°	19006
40°	13110
45°	8125
50°	4401
55°	2791
60°	2368
65°	2127
70°	1795
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8125 cd/sqm

TEST NUMBER: P1246691

CATALOG NUMBER: P3AS09R659024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.9	10.5
10°-20°	55.5	25.3
20°-30°	61.3	28.0
30°-40°	44.5	20.3
40°-50°	20.8	9.5
50°-60°	7.0	3.2
60°-70°	4.1	1.9
70°-80°	2.1	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	139.7	63.8
0°-40°	184.3	84.1
0°-60°	212.1	96.9
0°-90°	219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	219.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	254	
5°	247	23
15°	200	55
25°	134	61
35°	71	45
45°	26	21
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1246691

CATALOG NUMBER: P3AS09R659024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	253.9
2.5°	252.3
5°	246.6
7.5°	238.1
10°	227.0
12.5°	214.1
15°	199.6
17.5°	183.8
20°	167.7
22.5°	150.9
25°	134.5
27.5°	117.8
30°	101.4
32.5°	85.6
35°	71.0
37.5°	57.8
40°	45.8
42.5°	35.0
45°	26.2
47.5°	18.9
50°	12.9
52.5°	8.8
55°	7.3
57.5°	6.3
60°	5.4
62.5°	4.7
65°	4.1
67.5°	3.5
70°	2.8
72.5°	2.5
75°	1.9
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)