

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246710

Luminaire Tested: P3AS09R709024DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246710
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709024DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 650.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246710

CATALOG NUMBER: P3AS09R709024DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1246710

CATALOG NUMBER: P3AS09R709024DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	82		89	85	81		86	83	80		84	81	79
4	94	86	80	75		93	85	79	75		83	78	74		81	76	73		79	75	72
5	89	80	73	69		87	79	73	68		77	72	68		75	71	67		74	70	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	53		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	50	46		66	56	50	46		55	50	46		55	49	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125845
5°	124323
10°	120728
15°	115619
20°	108299
25°	98401
30°	85000
35°	67726
40°	49321
45°	32437
50°	15181
55°	4702
60°	4517
65°	4358
70°	4167
75°	4406
80°	4041
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32437 cd/sqm

TEST NUMBER: P1246710

CATALOG NUMBER: P3AS09R709024DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	8.2
10°-20°	142.5	21.9
20°-30°	185.3	28.5
30°-40°	157.2	24.2
40°-50°	81.1	12.5
50°-60°	15.6	2.4
60°-70°	8.5	1.3
70°-80°	5.2	0.8
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.0	58.6
0°-40°	538.2	82.8
0°-60°	634.9	97.7
0°-90°	650.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	650.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	565	53
15°	509	143
25°	407	185
35°	253	157
45°	105	81
55°	12	16
65°	8	8
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1246710

CATALOG NUMBER: P3AS09R709024DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	573.9
2.5°	571.9
5°	564.8
7.5°	554.5
10°	542.2
12.5°	526.7
15°	509.3
17.5°	488.0
20°	464.1
22.5°	437.0
25°	406.7
27.5°	372.5
30°	335.7
32.5°	295.0
35°	253.0
37.5°	211.7
40°	172.3
42.5°	135.6
45°	104.6
47.5°	76.8
50°	44.5
52.5°	19.4
55°	12.3
57.5°	11.6
60°	10.3
62.5°	9.7
65°	8.4
67.5°	7.7
70°	6.5
72.5°	5.8
75°	5.2
77.5°	3.9
80°	3.2
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)