

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246774

Luminaire Tested: P3AS13R129024DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129024DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 2400K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 782.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246774
CATALOG NUMBER: P3AS13R129024DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1246774
 CATALOG NUMBER: P3AS13R129024DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	668039
5°	592977
10°	411794
15°	243520
20°	138705
25°	79287
30°	43880
35°	23396
40°	12939
45°	7008
50°	4367
55°	3441
60°	2982
65°	2750
70°	2436
75°	2542
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7008 cd/sqm



TEST NUMBER: P1246774
 CATALOG NUMBER: P3AS13R129024DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.1	29.3
10°-20°	302.3	38.7
20°-30°	155.7	19.9
30°-40°	58.5	7.5
40°-50°	19.1	2.4
50°-60°	8.2	1.0
60°-70°	5.2	0.7
70°-80°	3.1	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.1	87.9
0°-40°	745.5	95.3
0°-60°	772.9	98.8
0°-90°	782.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	782.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3046	
5°	2694	229
15°	1073	302
25°	328	156
35°	87	58
45°	23	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1246774
CATALOG NUMBER: P3AS13R129024DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3046.5
1°	3040.4
2°	3000.5
3°	2924.4
4°	2824.2
5°	2693.9
6°	2546.3
7°	2384.3
8°	2204.3
9°	2026.5
10°	1849.4
12.5°	1423.0
15°	1072.7
17.5°	803.1
20°	594.4
22.5°	443.7
25°	327.7
27.5°	238.8
30°	173.3
32.5°	122.8
35°	87.4
37.5°	62.5
40°	45.2
42.5°	32.4
45°	22.6
47.5°	16.6
50°	12.8
52.5°	10.5
55°	9.0
57.5°	7.5
60°	6.8
62.5°	6.0
65°	5.3
67.5°	4.5
70°	3.8
72.5°	3.8
75°	3.0
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)