

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246780

Luminaire Tested: P3AS13R129024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 595.1 lumens
Efficiency: N/A
Efficacy: 38.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246780

CATALOG NUMBER: P3AS13R129024DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246780

CATALOG NUMBER: P3AS13R129024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150076
5°	146004
10°	133420
15°	116868
20°	100249
25°	83715
30°	66998
35°	50246
40°	36468
45°	23847
50°	14908
55°	10093
60°	8947
65°	8198
70°	7758
75°	7032
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23847 cd/sqm

TEST NUMBER: P1246780

CATALOG NUMBER: P3AS13R129024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	10.3
10°-20°	143.4	24.1
20°-30°	158.1	26.6
30°-40°	118.4	19.9
40°-50°	61.3	10.3
50°-60°	25.4	4.3
60°-70°	15.8	2.6
70°-80°	8.9	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.7	61.0
0°-40°	481.1	80.8
0°-60°	567.8	95.4
0°-90°	595.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	684	
5°	663	61
15°	515	143
25°	346	158
35°	188	118
45°	77	61
55°	26	25
65°	16	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1246780

CATALOG NUMBER: P3AS13R129024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	684.4
1°	685.2
2°	682.9
3°	678.4
4°	671.6
5°	663.3
6°	652.8
7°	641.5
8°	627.9
9°	613.6
10°	599.2
12.5°	557.8
15°	514.8
17.5°	471.9
20°	429.6
22.5°	386.7
25°	346.0
27.5°	305.3
30°	264.6
32.5°	224.6
35°	187.7
37.5°	156.0
40°	127.4
42.5°	101.0
45°	76.9
47.5°	58.0
50°	43.7
52.5°	32.4
55°	26.4
57.5°	23.4
60°	20.4
62.5°	18.1
65°	15.8
67.5°	13.6
70°	12.1
72.5°	9.8
75°	8.3
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)