

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246836

Luminaire Tested: P3AS13R209024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 331.0 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246836

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246836

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81879
5°	79683
10°	73301
15°	64518
20°	55328
25°	46503
30°	37575
35°	28590
40°	20352
45°	13428
50°	8324
55°	5467
60°	5000
65°	4566
70°	4296
75°	3897
80°	3662
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13428 cd/sqm

TEST NUMBER: P1246836

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.5	10.1
10°-20°	79.1	23.9
20°-30°	87.8	26.5
30°-40°	67.0	20.2
40°-50°	34.3	10.4
50°-60°	14.1	4.3
60°-70°	8.8	2.7
70°-80°	4.9	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	200.5	60.6
0°-40°	267.5	80.8
0°-60°	315.9	95.4
0°-90°	331.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	331.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	373	
5°	362	33
15°	284	79
25°	192	88
35°	107	67
45°	43	34
55°	14	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1246836

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	373.4
1°	373.8
2°	372.1
3°	370.0
4°	366.6
5°	362.0
6°	356.6
7°	350.7
8°	344.4
9°	336.8
10°	329.2
12.5°	307.4
15°	284.2
17.5°	260.7
20°	237.1
22.5°	213.6
25°	192.2
27.5°	170.7
30°	148.4
32.5°	127.4
35°	106.8
37.5°	88.7
40°	71.1
42.5°	55.9
45°	43.3
47.5°	32.8
50°	24.4
52.5°	18.1
55°	14.3
57.5°	13.0
60°	11.4
62.5°	10.1
65°	8.8
67.5°	7.6
70°	6.7
72.5°	5.5
75°	4.6
77.5°	3.8
80°	2.9
82.5°	2.1
85°	1.3
87.5°	0.4
90°	0.0

(END OF REPORT)