

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246863

Luminaire Tested: P3AS13R259024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 337.0 lumens
Efficiency: N/A
Efficacy: 23.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246863

CATALOG NUMBER: P3AS13R259024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246863

CATALOG NUMBER: P3AS13R259024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80103
5°	78186
10°	72455
15°	64518
20°	55445
25°	47132
30°	38791
35°	30222
40°	21755
45°	13800
50°	8153
55°	5620
60°	5175
65°	4774
70°	4296
75°	3897
80°	3662
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13800 cd/sqm

TEST NUMBER: P1246863

CATALOG NUMBER: P3AS13R259024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.9	9.8
10°-20°	78.9	23.4
20°-30°	89.1	26.5
30°-40°	70.5	20.9
40°-50°	35.6	10.6
50°-60°	14.3	4.2
60°-70°	9.1	2.7
70°-80°	5.0	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	201.0	59.6
0°-40°	271.5	80.6
0°-60°	321.4	95.4
0°-90°	337.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	337.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	365	
5°	355	33
15°	284	79
25°	195	89
35°	113	71
45°	44	36
55°	15	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1246863

CATALOG NUMBER: P3AS13R259024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	365.3
1°	365.3
2°	364.0
3°	361.9
4°	359.0
5°	355.2
6°	350.6
7°	345.1
8°	339.2
9°	332.5
10°	325.4
11°	317.4
12°	309.8
13°	301.0
14°	292.6
15°	284.2
17.5°	260.7
20°	237.6
22.5°	215.8
25°	194.8
27.5°	174.2
30°	153.2
32.5°	133.5
35°	112.9
37.5°	94.0
40°	76.0
42.5°	59.2
45°	44.5
47.5°	33.2
50°	23.9
52.5°	18.1
55°	14.7
57.5°	13.4
60°	11.8
62.5°	10.5
65°	9.2
67.5°	8.0
70°	6.7
72.5°	5.9
75°	4.6
77.5°	3.8
80°	2.9
82.5°	2.1
85°	1.3
87.5°	0.4



TEST NUMBER: P1246863
CATALOG NUMBER: P3AS13R259024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)