

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245582

Luminaire Tested: P3AS02R129024DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129024DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 2400K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 126.9 lumens
Efficiency: N/A
Efficacy: 34.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245582

CATALOG NUMBER: P3AS02R129024DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1245582

CATALOG NUMBER: P3AS02R129024DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	74	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	65		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		68	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	58		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	58	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54754
5°	50627
10°	40413
15°	30534
20°	23242
25°	17711
30°	12685
35°	8272
40°	5067
45°	3070
50°	2047
55°	1567
60°	1360
65°	1193
70°	1026
75°	1017
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3070 cd/sqm

TEST NUMBER: P1245582

CATALOG NUMBER: P3AS02R129024DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.4	16.0
10°-20°	37.6	29.6
20°-30°	33.5	26.4
30°-40°	19.8	15.6
40°-50°	8.1	6.4
50°-60°	3.8	3.0
60°-70°	2.3	1.8
70°-80°	1.2	0.9
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	91.4	72.0
0°-40°	111.2	87.6
0°-60°	123.1	97.0
0°-90°	126.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	126.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	250	
5°	230	20
15°	134	38
25°	73	33
35°	31	20
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245582

CATALOG NUMBER: P3AS02R129024DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	249.7
1°	249.1
2°	247.3
3°	243.6
4°	237.4
5°	230.0
6°	221.9
7°	212.4
8°	202.5
9°	192.4
10°	181.5
12.5°	156.5
15°	134.5
17.5°	115.5
20°	99.6
22.5°	85.6
25°	73.2
27.5°	61.3
30°	50.1
32.5°	40.0
35°	30.9
37.5°	23.7
40°	17.7
42.5°	13.2
45°	9.9
47.5°	7.6
50°	6.0
52.5°	4.9
55°	4.1
57.5°	3.5
60°	3.1
62.5°	2.7
65°	2.3
67.5°	2.1
70°	1.6
72.5°	1.4
75°	1.2
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)