

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245600

Luminaire Tested: P3AS02R159024DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1245600  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R159024DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 222.9 lumens  
Efficiency: N/A  
Efficacy: 61.9 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1245600

CATALOG NUMBER: P3AS02R159024DE010 E3DL1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1245600

CATALOG NUMBER: P3AS02R159024DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99  | 101 | 99  | 97  |  | 98  | 96  | 95  |  | 96  |
| 3   | 106 | 101 | 97  | 93  | 104 | 99  | 96  | 93  | 97  | 94  | 91  |  | 94  | 92  | 90  |  | 92  |
| 4   | 102 | 96  | 92  | 88  | 100 | 95  | 91  | 88  | 93  | 89  | 87  |  | 91  | 88  | 86  |  | 89  |
| 5   | 98  | 92  | 87  | 84  | 97  | 91  | 87  | 83  | 89  | 86  | 83  |  | 88  | 84  | 82  |  | 86  |
| 6   | 95  | 88  | 83  | 80  | 94  | 87  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 79  |  | 83  |
| 7   | 92  | 85  | 80  | 77  | 91  | 84  | 80  | 76  | 83  | 79  | 76  |  | 82  | 78  | 76  |  | 81  |
| 8   | 89  | 81  | 77  | 74  | 88  | 81  | 77  | 73  | 80  | 76  | 73  |  | 79  | 76  | 73  |  | 78  |
| 9   | 86  | 79  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 77  | 73  | 70  |  | 76  |
| 10  | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  |  | 74  | 71  | 68  |  | 74  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 190511 |
| 5°  | 169095 |
| 10° | 117433 |
| 15° | 69444  |
| 20° | 39553  |
| 25° | 22598  |
| 30° | 12508  |
| 35° | 6666   |
| 40° | 3693   |
| 45° | 1985   |
| 50° | 1262   |
| 55° | 994    |
| 60° | 833    |
| 65° | 778    |
| 70° | 705    |
| 75° | 763    |
| 80° | 505    |
| 85° | 503    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1985 cd/sqm

TEST NUMBER: P1245600

CATALOG NUMBER: P3AS02R159024DE010 E3DL1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 65.3   | 29.3      |
| 10°-20°   | 86.2   | 38.7      |
| 20°-30°   | 44.4   | 19.9      |
| 30°-40°   | 16.7   | 7.5       |
| 40°-50°   | 5.4    | 2.4       |
| 50°-60°   | 2.3    | 1.0       |
| 60°-70°   | 1.5    | 0.7       |
| 70°-80°   | 0.9    | 0.4       |
| 80°-90°   | 0.2    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 195.9  | 87.9      |
| 0°-40°    | 212.6  | 95.4      |
| 0°-60°    | 220.4  | 98.8      |
| 0°-90°    | 222.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 222.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 869 |      |
| 5°  | 768 | 65   |
| 15° | 306 | 86   |
| 25° | 93  | 44   |
| 35° | 25  | 17   |
| 45° | 6   | 5    |
| 55° | 3   | 2    |
| 65° | 2   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1245600

CATALOG NUMBER: P3AS02R159024DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 868.8 |
| 1°    | 867.0 |
| 2°    | 855.6 |
| 3°    | 834.0 |
| 4°    | 805.4 |
| 5°    | 768.2 |
| 6°    | 726.1 |
| 7°    | 679.9 |
| 8°    | 628.6 |
| 9°    | 577.9 |
| 10°   | 527.4 |
| 12.5° | 405.8 |
| 15°   | 305.9 |
| 17.5° | 229.0 |
| 20°   | 169.5 |
| 22.5° | 126.5 |
| 25°   | 93.4  |
| 27.5° | 68.1  |
| 30°   | 49.4  |
| 32.5° | 35.0  |
| 35°   | 24.9  |
| 37.5° | 17.8  |
| 40°   | 12.9  |
| 42.5° | 9.2   |
| 45°   | 6.4   |
| 47.5° | 4.7   |
| 50°   | 3.7   |
| 52.5° | 3.0   |
| 55°   | 2.6   |
| 57.5° | 2.1   |
| 60°   | 1.9   |
| 62.5° | 1.7   |
| 65°   | 1.5   |
| 67.5° | 1.3   |
| 70°   | 1.1   |
| 72.5° | 1.1   |
| 75°   | 0.9   |
| 77.5° | 0.6   |
| 80°   | 0.4   |
| 82.5° | 0.4   |
| 85°   | 0.2   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)