

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246948

Luminaire Tested: P3AS13R409024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1200.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246948

CATALOG NUMBER: P3AS13R409024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246948

CATALOG NUMBER: P3AS13R409024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	611662
5°	607262
10°	591350
15°	528244
20°	350264
25°	131209
30°	35094
35°	13733
40°	4924
45°	2357
50°	716
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2357 cd/sqm

TEST NUMBER: P1246948

CATALOG NUMBER: P3AS13R409024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.3	21.7
10°-20°	616.6	51.4
20°-30°	279.6	23.3
30°-40°	36.2	3.0
40°-50°	6.3	0.5
50°-60°	0.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1156.5	96.4
0°-40°	1192.7	99.4
0°-60°	1199.7	100.0
0°-90°	1200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1200.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2789	
5°	2759	260
15°	2327	617
25°	542	280
35°	51	36
45°	8	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246948

CATALOG NUMBER: P3AS13R409024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2789.4
1°	2787.7
2°	2783.5
3°	2777.2
4°	2769.3
5°	2758.8
6°	2746.6
7°	2731.5
8°	2713.0
9°	2687.8
10°	2655.8
11°	2618.4
12°	2568.5
13°	2506.7
14°	2426.0
15°	2326.9
16°	2200.5
17°	2056.4
18°	1883.3
19°	1700.5
20°	1501.0
21°	1301.5
22°	1104.8
23°	909.1
24°	716.7
25°	542.3
26°	401.6
27°	294.1
28°	221.0
29°	171.8
30°	138.6
31°	114.7
32°	95.8
32.5°	87.4
33°	79.0
34°	64.3
35°	51.3
36°	40.3
37°	31.9
37.5°	28.6
38°	25.2
39°	21.0
40°	17.2
42.5°	11.3
45°	7.6



TEST NUMBER: P1246948

CATALOG NUMBER: P3AS13R409024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	4.6
50°	2.1
52.5°	0.8
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)