

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246949

Luminaire Tested: P3AS13R409024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 489.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246949

CATALOG NUMBER: P3AS13R409024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246949

CATALOG NUMBER: P3AS13R409024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216386
5°	210081
10°	190644
15°	157504
20°	113620
25°	70262
30°	38056
35°	19675
40°	10706
45°	5985
50°	3002
55°	2256
60°	2017
65°	1972
70°	1859
75°	1779
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5985 cd/sqm

TEST NUMBER: P1246949

CATALOG NUMBER: P3AS13R409024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.0	18.0
10°-20°	188.9	38.6
20°-30°	134.8	27.6
30°-40°	49.6	10.2
40°-50°	15.6	3.2
50°-60°	5.4	1.1
60°-70°	3.7	0.8
70°-80°	2.2	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	411.7	84.2
0°-40°	461.4	94.3
0°-60°	482.4	98.7
0°-90°	489.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	489.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	987	
5°	954	88
15°	694	189
25°	290	135
35°	74	50
45°	19	16
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1246949

CATALOG NUMBER: P3AS13R409024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	986.8
2.5°	979.2
5°	954.4
7.5°	913.3
10°	856.2
12.5°	783.6
15°	693.8
17.5°	593.1
20°	486.9
22.5°	382.4
25°	290.4
27.5°	213.2
30°	150.3
32.5°	105.4
35°	73.5
37.5°	52.0
40°	37.4
42.5°	26.9
45°	19.3
47.5°	13.0
50°	8.8
52.5°	6.3
55°	5.9
57.5°	5.5
60°	4.6
62.5°	4.2
65°	3.8
67.5°	3.4
70°	2.9
72.5°	2.5
75°	2.1
77.5°	1.7
80°	1.3
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)