

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245611

Luminaire Tested: P3AS02R159024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 65.0 lumens
Efficiency: N/A
Efficacy: 18.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245611

CATALOG NUMBER: P3AS02R159024DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1245611

CATALOG NUMBER: P3AS02R159024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	73		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28024
5°	25908
10°	20685
15°	15619
20°	11901
25°	9073
30°	6482
35°	4230
40°	2605
45°	1582
50°	1058
55°	803
60°	702
65°	623
70°	513
75°	508
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1582 cd/sqm

TEST NUMBER: P1245611

CATALOG NUMBER: P3AS02R159024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.4	16.0
10°-20°	19.2	29.6
20°-30°	17.1	26.3
30°-40°	10.1	15.6
40°-50°	4.2	6.4
50°-60°	1.9	3.0
60°-70°	1.2	1.9
70°-80°	0.6	0.9
80°-90°	0.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	46.8	72.0
0°-40°	56.9	87.6
0°-60°	63.0	97.0
0°-90°	65.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	65.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	128	
5°	118	10
15°	69	19
25°	38	17
35°	16	10
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245611

CATALOG NUMBER: P3AS02R159024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	127.8
1°	127.5
2°	126.6
3°	124.7
4°	121.5
5°	117.7
6°	113.6
7°	108.7
8°	103.7
9°	98.5
10°	92.9
12.5°	80.1
15°	68.8
17.5°	59.1
20°	51.0
22.5°	43.8
25°	37.5
27.5°	31.3
30°	25.6
32.5°	20.5
35°	15.8
37.5°	12.1
40°	9.1
42.5°	6.8
45°	5.1
47.5°	3.9
50°	3.1
52.5°	2.5
55°	2.1
57.5°	1.8
60°	1.6
62.5°	1.4
65°	1.2
67.5°	1.1
70°	0.8
72.5°	0.7
75°	0.6
77.5°	0.4
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)