

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247044

Luminaire Tested: P3AS13R559024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 306.0 lumens
Efficiency: N/A
Efficacy: 21.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247044
CATALOG NUMBER: P3AS13R559024DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247044
 CATALOG NUMBER: P3AS13R559024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83239
5°	81158
10°	75438
15°	67197
20°	57102
25°	46067
30°	35119
35°	24976
40°	16488
45°	9768
50°	5731
55°	3517
60°	3114
65°	2854
70°	2436
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9768 cd/sqm



TEST NUMBER: P1247044
 CATALOG NUMBER: P3AS13R559024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.2	11.2
10°-20°	82.1	26.8
20°-30°	86.9	28.4
30°-40°	58.7	19.2
40°-50°	25.7	8.4
50°-60°	9.2	3.0
60°-70°	5.4	1.8
70°-80°	2.8	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.2	66.4
0°-40°	261.9	85.6
0°-60°	296.8	97.0
0°-90°	306.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	306.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	380	
5°	369	34
15°	296	82
25°	190	87
35°	93	59
45°	32	26
55°	9	9
65°	6	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1247044
CATALOG NUMBER: P3AS13R559024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	379.6
2.5°	376.7
5°	368.7
7.5°	355.6
10°	338.8
12.5°	318.7
15°	296.0
17.5°	270.7
20°	244.7
22.5°	217.3
25°	190.4
27.5°	164.0
30°	138.7
32.5°	114.8
35°	93.3
37.5°	74.0
40°	57.6
42.5°	43.3
45°	31.5
47.5°	23.1
50°	16.8
52.5°	11.8
55°	9.2
57.5°	8.4
60°	7.1
62.5°	6.3
65°	5.5
67.5°	4.6
70°	3.8
72.5°	3.4
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)