

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245711

Luminaire Tested: P3AS02R359024DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359024DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245711

CATALOG NUMBER: P3AS02R359024DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1245711

CATALOG NUMBER: P3AS02R359024DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	96	105	101	98	95	98	96	93	96	94	92	94	92	91	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178012
5°	174378
10°	162233
15°	118934
20°	60905
25°	21945
30°	8558
35°	2998
40°	1231
45°	341
50°	307
55°	344
60°	263
65°	208
70°	256
75°	339
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 55°

Luminance: 344 cd/sqm

TEST NUMBER: P1245711

CATALOG NUMBER: P3AS02R359024DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	27.1
10°-20°	138.6	50.8
20°-30°	49.1	18.0
30°-40°	8.6	3.2
40°-50°	1.3	0.5
50°-60°	0.7	0.3
60°-70°	0.5	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.5	95.8
0°-40°	270.1	99.0
0°-60°	272.1	99.7
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	812	
5°	792	74
15°	524	139
25°	91	49
35°	11	9
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1245711

CATALOG NUMBER: P3AS02R359024DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	811.8
1°	811.6
2°	809.0
3°	804.1
4°	799.6
5°	792.2
6°	784.7
7°	776.3
8°	766.0
9°	749.9
10°	728.6
11°	699.2
12°	663.7
13°	621.5
14°	575.1
15°	523.9
17.5°	390.2
20°	261.0
22.5°	157.4
25°	90.7
27.5°	54.2
30°	33.8
32.5°	19.6
35°	11.2
37.5°	7.1
40°	4.3
42.5°	2.1
45°	1.1
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1245711
CATALOG NUMBER: P3AS02R359024DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)