

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245718

Luminaire Tested: P3AS02R359024DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1245718  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359024DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 226.0 lumens  
Efficiency: N/A  
Efficacy: 62.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1245718

CATALOG NUMBER: P3AS02R359024DE010 E3DL1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1245718

CATALOG NUMBER: P3AS02R359024DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 109 | 107 |  | 112 | 109 | 107 | 106 |  | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  | 97  | 96  |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 93  | 91  |
| 3   | 105 | 99  | 95  | 91  |  | 103 | 98  | 94  | 90  |  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 88  | 86  |
| 4   | 100 | 94  | 89  | 85  |  | 99  | 93  | 88  | 85  |  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 82  |
| 5   | 96  | 89  | 84  | 80  |  | 95  | 88  | 83  | 80  |  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 78  |
| 6   | 92  | 85  | 80  | 76  |  | 91  | 84  | 79  | 76  |  | 83  | 78  | 75  |  | 81  | 77  | 75  |  | 80  | 77  | 74  |
| 7   | 89  | 81  | 76  | 72  |  | 88  | 80  | 75  | 72  |  | 79  | 75  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 71  |
| 8   | 85  | 77  | 72  | 69  |  | 84  | 77  | 72  | 69  |  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 68  |
| 9   | 82  | 74  | 69  | 66  |  | 81  | 74  | 69  | 65  |  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 68  | 65  |
| 10  | 79  | 71  | 66  | 63  |  | 78  | 71  | 66  | 63  |  | 70  | 66  | 63  |  | 69  | 65  | 62  |  | 69  | 65  | 62  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 113982 |
| 5°  | 109553 |
| 10° | 95456  |
| 15° | 73099  |
| 20° | 48911  |
| 25° | 29590  |
| 30° | 16990  |
| 35° | 9503   |
| 40° | 5038   |
| 45° | 2605   |
| 50° | 1262   |
| 55° | 994    |
| 60° | 921    |
| 65° | 778    |
| 70° | 833    |
| 75° | 763    |
| 80° | 758    |
| 85° | 503    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 2605 cd/sqm

TEST NUMBER: P1245718

CATALOG NUMBER: P3AS02R359024DE010 E3DL1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 45.3   | 20.0      |
| 10°-20°   | 87.7   | 38.8      |
| 20°-30°   | 57.4   | 25.4      |
| 30°-40°   | 23.3   | 10.3      |
| 40°-50°   | 7.0    | 3.1       |
| 50°-60°   | 2.4    | 1.1       |
| 60°-70°   | 1.6    | 0.7       |
| 70°-80°   | 0.9    | 0.4       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 190.5  | 84.3      |
| 0°-40°    | 213.8  | 94.6      |
| 0°-60°    | 223.2  | 98.8      |
| 0°-90°    | 226.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 226.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 520 |      |
| 5°  | 498 | 45   |
| 15° | 322 | 88   |
| 25° | 122 | 57   |
| 35° | 36  | 23   |
| 45° | 8   | 7    |
| 55° | 3   | 2    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1245718

CATALOG NUMBER: P3AS02R359024DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 519.8 |
| 1°    | 519.0 |
| 2°    | 516.6 |
| 3°    | 511.9 |
| 4°    | 506.3 |
| 5°    | 497.7 |
| 6°    | 486.9 |
| 7°    | 474.9 |
| 8°    | 461.3 |
| 9°    | 445.9 |
| 10°   | 428.7 |
| 11°   | 409.5 |
| 12°   | 389.5 |
| 13°   | 367.2 |
| 14°   | 345.9 |
| 15°   | 322.0 |
| 17.5° | 264.2 |
| 20°   | 209.6 |
| 22.5° | 161.2 |
| 25°   | 122.3 |
| 27.5° | 91.1  |
| 30°   | 67.1  |
| 32.5° | 49.2  |
| 35°   | 35.5  |
| 37.5° | 25.2  |
| 40°   | 17.6  |
| 42.5° | 12.3  |
| 45°   | 8.4   |
| 47.5° | 5.6   |
| 50°   | 3.7   |
| 52.5° | 2.8   |
| 55°   | 2.6   |
| 57.5° | 2.4   |
| 60°   | 2.1   |
| 62.5° | 1.9   |
| 65°   | 1.5   |
| 67.5° | 1.3   |
| 70°   | 1.3   |
| 72.5° | 1.1   |
| 75°   | 0.9   |
| 77.5° | 0.6   |
| 80°   | 0.6   |
| 82.5° | 0.4   |
| 85°   | 0.2   |
| 87.5° | 0.2   |



TEST NUMBER: P1245718

CATALOG NUMBER: P3AS02R359024DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)