

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247060

Luminaire Tested: P3AS13R609024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1027.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247060

CATALOG NUMBER: P3AS13R609024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247060

CATALOG NUMBER: P3AS13R609024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269079
5°	254017
10°	247424
15°	241772
20°	224790
25°	200963
30°	153492
35°	88606
40°	34407
45°	14327
50°	3138
55°	497
60°	351
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14327 cd/sqm

TEST NUMBER: P1247060

CATALOG NUMBER: P3AS13R609024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	10.6
10°-20°	296.7	28.9
20°-30°	371.6	36.2
30°-40°	207.7	20.2
40°-50°	39.5	3.8
50°-60°	2.0	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.2	75.7
0°-40°	984.9	95.9
0°-60°	1026.4	99.9
0°-90°	1027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1227	
5°	1154	109
15°	1065	297
25°	831	372
35°	331	208
45°	46	39
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247060

CATALOG NUMBER: P3AS13R609024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1227.1
1°	1222.1
2°	1206.1
3°	1187.2
4°	1169.6
5°	1154.0
6°	1142.3
7°	1132.2
8°	1124.6
9°	1117.5
10°	1111.2
11°	1104.9
12°	1097.7
13°	1088.9
14°	1078.4
15°	1065.0
16°	1048.6
17°	1030.1
18°	1009.1
19°	985.2
20°	963.3
21°	939.8
22°	915.4
23°	889.8
24°	861.6
25°	830.6
26°	794.0
27°	753.3
28°	707.5
29°	658.7
30°	606.2
31°	553.3
32°	498.7
32.5°	468.8
33°	442.0
34°	386.1
35°	331.0
36°	281.5
37°	229.0
37.5°	205.0
38°	181.5
39°	146.2
40°	120.2
42.5°	73.1
45°	46.2



TEST NUMBER: P1247060

CATALOG NUMBER: P3AS13R609024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	25.6
50°	9.2
52.5°	2.1
55°	1.3
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)