

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245719

Luminaire Tested: P3AS02R359024DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359024DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 226.0 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245719

CATALOG NUMBER: P3AS02R359024DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1245719

CATALOG NUMBER: P3AS02R359024DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	70
8	85	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71	68	65	64
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113982
5°	109553
10°	95456
15°	73099
20°	48911
25°	29590
30°	16990
35°	9503
40°	5038
45°	2605
50°	1262
55°	994
60°	921
65°	778
70°	833
75°	763
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2605 cd/sqm

TEST NUMBER: P1245719

CATALOG NUMBER: P3AS02R359024DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.3	20.0
10°-20°	87.7	38.8
20°-30°	57.4	25.4
30°-40°	23.3	10.3
40°-50°	7.0	3.1
50°-60°	2.4	1.1
60°-70°	1.6	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.5	84.3
0°-40°	213.8	94.6
0°-60°	223.2	98.8
0°-90°	226.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	226.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	520	
5°	498	45
15°	322	88
25°	122	57
35°	36	23
45°	8	7
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245719

CATALOG NUMBER: P3AS02R359024DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	519.8
1°	519.0
2°	516.6
3°	511.9
4°	506.3
5°	497.7
6°	486.9
7°	474.9
8°	461.3
9°	445.9
10°	428.7
11°	409.5
12°	389.5
13°	367.2
14°	345.9
15°	322.0
17.5°	264.2
20°	209.6
22.5°	161.2
25°	122.3
27.5°	91.1
30°	67.1
32.5°	49.2
35°	35.5
37.5°	25.2
40°	17.6
42.5°	12.3
45°	8.4
47.5°	5.6
50°	3.7
52.5°	2.8
55°	2.6
57.5°	2.4
60°	2.1
62.5°	1.9
65°	1.5
67.5°	1.3
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.6
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1245719
CATALOG NUMBER: P3AS02R359024DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)