

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247072

Luminaire Tested: P3AS13R609024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 707.0 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247072

CATALOG NUMBER: P3AS13R609024DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247072

CATALOG NUMBER: P3AS13R609024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125494
5°	124103
10°	119793
15°	113168
20°	104332
25°	94457
30°	83861
35°	71661
40°	56992
45°	40190
50°	24016
55°	12119
60°	11666
65°	10689
70°	9873
75°	9489
80°	8713
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40190 cd/sqm

TEST NUMBER: P1247072

CATALOG NUMBER: P3AS13R609024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.0	7.5
10°-20°	139.3	19.7
20°-30°	178.9	25.3
30°-40°	165.9	23.5
40°-50°	101.0	14.3
50°-60°	33.6	4.8
60°-70°	20.5	2.9
70°-80°	11.6	1.6
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.2	52.5
0°-40°	537.1	76.0
0°-60°	671.7	95.0
0°-90°	707.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	572	
5°	564	53
15°	498	139
25°	390	179
35°	268	166
45°	130	101
55°	32	34
65°	21	20
75°	11	12
85°	3	3
90°	0	

TEST NUMBER: P1247072

CATALOG NUMBER: P3AS13R609024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	572.3
2.5°	569.8
5°	563.8
7.5°	552.6
10°	538.0
12.5°	520.0
15°	498.5
17.5°	473.7
20°	447.1
22.5°	418.7
25°	390.4
27.5°	361.3
30°	331.2
32.5°	301.2
35°	267.7
37.5°	232.5
40°	199.1
42.5°	163.9
45°	129.6
47.5°	100.4
50°	70.4
52.5°	42.0
55°	31.7
57.5°	29.2
60°	26.6
62.5°	23.2
65°	20.6
67.5°	18.0
70°	15.4
72.5°	12.9
75°	11.2
77.5°	8.6
80°	6.9
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0

(END OF REPORT)