

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247118

Luminaire Tested: P3AS13R709024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1023.0 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247118

CATALOG NUMBER: P3AS13R709024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247118

CATALOG NUMBER: P3AS13R709024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198910
5°	187563
10°	177841
15°	174643
20°	168341
25°	158695
30°	157569
35°	137219
40°	88766
45°	41958
50°	5868
55°	497
60°	351
65°	415
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41958 cd/sqm

TEST NUMBER: P1247118

CATALOG NUMBER: P3AS13R709024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.6	7.8
10°-20°	216.0	21.1
20°-30°	305.6	29.9
30°-40°	307.1	30.0
40°-50°	110.5	10.8
50°-60°	3.0	0.3
60°-70°	0.6	0.1
70°-80°	0.4	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.3	58.8
0°-40°	908.4	88.8
0°-60°	1021.8	99.9
0°-90°	1023.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1023.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	907	
5°	852	80
15°	769	216
25°	656	306
35°	513	307
45°	135	110
55°	1	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247118

CATALOG NUMBER: P3AS13R709024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	907.1
1°	904.6
2°	896.6
3°	884.0
4°	868.1
5°	852.1
6°	837.0
7°	825.2
8°	814.7
9°	806.3
10°	798.7
11°	792.4
12°	786.5
13°	780.7
14°	775.2
15°	769.3
16°	762.2
17°	754.6
18°	745.4
19°	734.0
20°	721.4
21°	707.6
22°	693.7
23°	680.2
24°	667.2
25°	655.9
26°	647.9
27°	641.6
28°	636.5
29°	630.7
30°	622.3
31°	610.1
32°	592.8
32.5°	583.2
33°	570.2
34°	544.5
35°	512.6
36°	477.3
37°	437.4
37.5°	418.9
38°	393.7
39°	348.7
40°	310.1
42.5°	214.7
45°	135.3



TEST NUMBER: P1247118

CATALOG NUMBER: P3AS13R709024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	72.7
50°	17.2
52.5°	2.1
55°	1.3
57.5°	1.3
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)