

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245845

Luminaire Tested: P3AS02R559024DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559024DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 156.0 lumens
Efficiency: N/A
Efficacy: 43.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245845

CATALOG NUMBER: P3AS02R559024DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1245845

CATALOG NUMBER: P3AS02R559024DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42431
5°	41382
10°	38454
15°	34257
20°	29099
25°	23493
30°	17901
35°	12742
40°	8416
45°	4993
50°	2934
55°	1797
60°	1579
65°	1453
70°	1218
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4993 cd/sqm

TEST NUMBER: P1245845

CATALOG NUMBER: P3AS02R559024DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.5	11.2
10°-20°	41.8	26.8
20°-30°	44.3	28.4
30°-40°	29.9	19.2
40°-50°	13.1	8.4
50°-60°	4.7	3.0
60°-70°	2.8	1.8
70°-80°	1.5	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.6	66.4
0°-40°	133.5	85.6
0°-60°	151.4	97.0
0°-90°	156.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	156.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	194	
5°	188	17
15°	151	42
25°	97	44
35°	48	30
45°	16	13
55°	5	5
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245845

CATALOG NUMBER: P3AS02R559024DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	193.5
2.5°	192.0
5°	188.0
7.5°	181.3
10°	172.7
12.5°	162.5
15°	150.9
17.5°	138.0
20°	124.7
22.5°	110.8
25°	97.1
27.5°	83.6
30°	70.7
32.5°	58.5
35°	47.6
37.5°	37.7
40°	29.4
42.5°	22.1
45°	16.1
47.5°	11.8
50°	8.6
52.5°	6.0
55°	4.7
57.5°	4.3
60°	3.6
62.5°	3.2
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)