

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245857

Luminaire Tested: P3AS02R609024DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609024DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 257.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245857
CATALOG NUMBER: P3AS02R609024DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1245857

CATALOG NUMBER: P3AS02R609024DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67			67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59			59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67341
5°	63570
10°	61923
15°	60500
20°	56262
25°	50277
30°	38411
35°	22165
40°	8616
45°	3597
50°	785
55°	115
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3597 cd/sqm



TEST NUMBER: P1245857
 CATALOG NUMBER: P3AS02R609024DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.3	10.6
10°-20°	74.2	28.9
20°-30°	93.0	36.2
30°-40°	52.0	20.2
40°-50°	9.9	3.8
50°-60°	0.5	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.5	75.7
0°-40°	246.5	95.9
0°-60°	256.8	99.9
0°-90°	257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	307	
5°	289	27
15°	266	74
25°	208	93
35°	83	52
45°	12	10
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1245857
CATALOG NUMBER: P3AS02R609024DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	307.1
1°	305.8
2°	301.8
3°	297.1
4°	292.7
5°	288.8
6°	285.8
7°	283.3
8°	281.4
9°	279.6
10°	278.1
11°	276.5
12°	274.7
13°	272.5
14°	269.9
15°	266.5
16°	262.4
17°	257.8
18°	252.5
19°	246.5
20°	241.1
21°	235.2
22°	229.1
23°	222.7
24°	215.6
25°	207.8
26°	198.7
27°	188.5
28°	177.0
29°	164.8
30°	151.7
31°	138.5
32°	124.8
32.5°	117.3
33°	110.6
34°	96.6
35°	82.8
36°	70.4
37°	57.3
37.5°	51.3
38°	45.4
39°	36.6
40°	30.1
42.5°	18.3
45°	11.6



TEST NUMBER: P1245857
CATALOG NUMBER: P3AS02R609024DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.4
50°	2.3
52.5°	0.5
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)