

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247258

Luminaire Tested: P3AS17R309024DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309024DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1446.0 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247258

CATALOG NUMBER: P3AS17R309024DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1247258

CATALOG NUMBER: P3AS17R309024DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	100	96	93	103	99	95	92	97	94	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	88	85		90	87	85		89
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	78	76	82	78	76		81	78	76		80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1177537
5°	1155269
10°	1022715
15°	647949
20°	245955
25°	72827
30°	28764
35°	8807
40°	3893
45°	1395
50°	1160
55°	879
60°	1009
65°	1193
70°	705
75°	932
80°	1389
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1395 cd/sqm

TEST NUMBER: P1247258

CATALOG NUMBER: P3AS17R309024DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	482.5	33.4
10°-20°	751.9	52.0
20°-30°	174.6	12.1
30°-40°	27.0	1.9
40°-50°	4.6	0.3
50°-60°	2.2	0.2
60°-70°	1.8	0.1
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1409.0	97.4
0°-40°	1436.0	99.3
0°-60°	1442.8	99.8
0°-90°	1446.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1446.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5370	
5°	5248	482
15°	2854	752
25°	301	175
35°	33	27
45°	4	5
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1247258

CATALOG NUMBER: P3AS17R309024DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5370.0
1°	5366.6
2°	5351.8
3°	5326.8
4°	5295.0
5°	5248.4
6°	5190.5
7°	5104.2
8°	4986.1
9°	4812.3
10°	4593.1
11°	4310.3
12°	3991.1
13°	3636.8
14°	3247.2
15°	2854.2
17.5°	1867.2
20°	1054.0
22.5°	538.4
25°	301.0
27.5°	185.1
30°	113.6
32.5°	61.3
35°	32.9
37.5°	21.6
40°	13.6
42.5°	8.0
45°	4.5
47.5°	3.4
50°	3.4
52.5°	2.3
55°	2.3
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1247258

CATALOG NUMBER: P3AS17R309024DE010 E3CB1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)