

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245924

Luminaire Tested: P3AS02R709024DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709024DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 215.9 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245924

CATALOG NUMBER: P3AS02R709024DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1245924

CATALOG NUMBER: P3AS02R709024DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41817
5°	41316
10°	40124
15°	38411
20°	35983
25°	32687
30°	28232
35°	22513
40°	16402
45°	10761
50°	5049
55°	1567
60°	1491
65°	1453
70°	1346
75°	1440
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10761 cd/sqm

TEST NUMBER: P1245924

CATALOG NUMBER: P3AS02R709024DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.7	8.2
10°-20°	47.4	21.9
20°-30°	61.6	28.5
30°-40°	52.2	24.2
40°-50°	26.9	12.5
50°-60°	5.2	2.4
60°-70°	2.8	1.3
70°-80°	1.7	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	126.6	58.6
0°-40°	178.8	82.8
0°-60°	210.9	97.7
0°-90°	215.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	215.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	191	
5°	188	18
15°	169	47
25°	135	62
35°	84	52
45°	35	27
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1245924

CATALOG NUMBER: P3AS02R709024DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	190.7
2.5°	190.1
5°	187.7
7.5°	184.3
10°	180.2
12.5°	175.0
15°	169.2
17.5°	162.2
20°	154.2
22.5°	145.2
25°	135.1
27.5°	123.8
30°	111.5
32.5°	98.0
35°	84.1
37.5°	70.4
40°	57.3
42.5°	45.0
45°	34.7
47.5°	25.5
50°	14.8
52.5°	6.4
55°	4.1
57.5°	3.9
60°	3.4
62.5°	3.2
65°	2.8
67.5°	2.6
70°	2.1
72.5°	1.9
75°	1.7
77.5°	1.3
80°	1.1
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)