

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247279

Luminaire Tested: P3AS17R309024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 359.0 lumens
Efficiency: N/A
Efficacy: 16.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247279

CATALOG NUMBER: P3AS17R309024DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1247279

CATALOG NUMBER: P3AS17R309024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122688
5°	118864
10°	107101
15°	88582
20°	68583
25°	51438
30°	37348
35°	24895
40°	15286
45°	8962
50°	5492
55°	4473
60°	3903
65°	3165
70°	2885
75°	2796
80°	2147
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8962 cd/sqm

TEST NUMBER: P1247279

CATALOG NUMBER: P3AS17R309024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	13.8
10°-20°	107.5	29.9
20°-30°	97.8	27.2
30°-40°	59.1	16.5
40°-50°	23.7	6.6
50°-60°	10.5	2.9
60°-70°	6.3	1.8
70°-80°	3.5	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.9	71.0
0°-40°	314.0	87.5
0°-60°	348.2	97.0
0°-90°	359.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	359.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	540	50
15°	390	107
25°	213	98
35°	93	59
45°	29	24
55°	12	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1247279

CATALOG NUMBER: P3AS17R309024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	559.5
1°	558.9
2°	556.7
3°	552.8
4°	547.2
5°	540.0
6°	531.1
7°	521.6
8°	509.4
9°	495.4
10°	481.0
11°	464.3
12°	446.4
13°	428.6
14°	409.2
15°	390.2
17.5°	340.7
20°	293.9
22.5°	250.5
25°	212.6
27.5°	178.1
30°	147.5
32.5°	119.1
35°	93.0
37.5°	71.3
40°	53.4
42.5°	39.0
45°	28.9
47.5°	21.7
50°	16.1
52.5°	12.8
55°	11.7
57.5°	10.0
60°	8.9
62.5°	7.2
65°	6.1
67.5°	5.6
70°	4.5
72.5°	3.9
75°	3.3
77.5°	2.8
80°	1.7
82.5°	1.1
85°	1.1
87.5°	0.6



TEST NUMBER: P1247279

CATALOG NUMBER: P3AS17R309024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)