

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247299

Luminaire Tested: P3AS17R359024DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247299  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359024DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 737.0 lumens  
Efficiency: N/A  
Efficacy: 34.8 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247299  
CATALOG NUMBER: P3AS17R359024DE010 E3DL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1247299  
 CATALOG NUMBER: P3AS17R359024DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	236889
5°	231058
10°	211241
15°	179297
20°	141926
25°	107353
30°	78164
35°	52869
40°	32489
45°	18638
50°	11224
55°	9099
60°	7982
65°	7057
70°	5834
75°	5761
80°	5683
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18638 cd/sqm



TEST NUMBER: P1247299  
 CATALOG NUMBER: P3AS17R359024DE010 E3DL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.0	13.2
10°-20°	217.7	29.5
20°-30°	203.7	27.6
30°-40°	124.7	16.9
40°-50°	49.1	6.7
50°-60°	21.6	2.9
60°-70°	13.5	1.8
70°-80°	7.2	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.4	70.3
0°-40°	643.1	87.3
0°-60°	713.9	96.9
0°-90°	737.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	737.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1080	
5°	1050	97
15°	790	218
25°	444	204
35°	198	125
45°	60	49
55°	24	22
65°	14	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1247299  
CATALOG NUMBER: P3AS17R359024DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1080.3
1°	1081.4
2°	1078.0
3°	1071.2
4°	1061.0
5°	1049.7
6°	1034.9
7°	1017.9
8°	997.5
9°	974.8
10°	948.7
11°	921.4
12°	891.9
13°	860.2
14°	825.0
15°	789.8
17.5°	699.0
20°	608.2
22.5°	520.9
25°	443.7
27.5°	372.2
30°	308.7
32.5°	249.7
35°	197.5
37.5°	150.9
40°	113.5
42.5°	81.7
45°	60.1
47.5°	43.1
50°	32.9
52.5°	27.2
55°	23.8
57.5°	20.4
60°	18.2
62.5°	15.9
65°	13.6
67.5°	11.3
70°	9.1
72.5°	7.9
75°	6.8
77.5°	5.7
80°	4.5
82.5°	3.4
85°	2.3
87.5°	1.1



TEST NUMBER: P1247299  
CATALOG NUMBER: P3AS17R359024DE010 E3DL1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)