

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247332

Luminaire Tested: P3AS17R409024DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409024DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1323.0 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247332
CATALOG NUMBER: P3AS17R409024DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1247332
 CATALOG NUMBER: P3AS17R409024DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	585414
5°	568411
10°	515822
15°	426132
20°	307397
25°	190124
30°	102927
35°	53190
40°	28940
45°	16188
50°	8119
55°	6079
60°	5482
65°	5292
70°	5065
75°	4829
80°	4293
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16188 cd/sqm



TEST NUMBER: P1247332
 CATALOG NUMBER: P3AS17R409024DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.0	18.0
10°-20°	511.1	38.6
20°-30°	364.8	27.6
30°-40°	134.3	10.1
40°-50°	42.3	3.2
50°-60°	14.7	1.1
60°-70°	10.1	0.8
70°-80°	6.0	0.5
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1113.9	84.2
0°-40°	1248.2	94.3
0°-60°	1305.2	98.7
0°-90°	1323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1323.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2670	
5°	2582	238
15°	1877	511
25°	786	365
35°	199	134
45°	52	42
55°	16	15
65°	10	10
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1247332
CATALOG NUMBER: P3AS17R409024DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2669.7
2.5°	2649.3
5°	2582.3
7.5°	2471.0
10°	2316.6
12.5°	2120.1
15°	1877.1
17.5°	1604.6
20°	1317.3
22.5°	1034.5
25°	785.8
27.5°	576.9
30°	406.5
32.5°	285.0
35°	198.7
37.5°	140.8
40°	101.1
42.5°	72.7
45°	52.2
47.5°	35.2
50°	23.8
52.5°	17.0
55°	15.9
57.5°	14.8
60°	12.5
62.5°	11.4
65°	10.2
67.5°	9.1
70°	7.9
72.5°	6.8
75°	5.7
77.5°	4.5
80°	3.4
82.5°	2.3
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)