

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246020

Luminaire Tested: P3AS05R159024DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246020
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159024DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 349.0 lumens
Efficiency: N/A
Efficacy: 48.5 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246020

CATALOG NUMBER: P3AS05R159024DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1246020

CATALOG NUMBER: P3AS05R159024DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88041
5°	85648
10°	78266
15°	68559
20°	58805
25°	49092
30°	39297
35°	29473
40°	21383
45°	13986
50°	8733
55°	5926
60°	5219
65°	4825
70°	4552
75°	4151
80°	3915
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13986 cd/sqm

TEST NUMBER: P1246020

CATALOG NUMBER: P3AS05R159024DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	10.3
10°-20°	84.1	24.1
20°-30°	92.7	26.6
30°-40°	69.4	19.9
40°-50°	36.0	10.3
50°-60°	14.9	4.3
60°-70°	9.2	2.7
70°-80°	5.2	1.5
80°-90°	1.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.8	61.0
0°-40°	282.2	80.9
0°-60°	333.0	95.4
0°-90°	349.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	349.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	402	
5°	389	36
15°	302	84
25°	203	93
35°	110	69
45°	45	36
55°	16	15
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1246020

CATALOG NUMBER: P3AS05R159024DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	401.5
1°	401.9
2°	400.6
3°	397.9
4°	393.9
5°	389.1
6°	382.9
7°	376.3
8°	368.3
9°	359.9
10°	351.5
12.5°	327.2
15°	302.0
17.5°	276.8
20°	252.0
22.5°	226.8
25°	202.9
27.5°	179.1
30°	155.2
32.5°	131.8
35°	110.1
37.5°	91.5
40°	74.7
42.5°	59.2
45°	45.1
47.5°	34.0
50°	25.6
52.5°	19.0
55°	15.5
57.5°	13.7
60°	11.9
62.5°	10.6
65°	9.3
67.5°	8.0
70°	7.1
72.5°	5.7
75°	4.9
77.5°	4.0
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.4
90°	0.0

(END OF REPORT)