

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246047

Luminaire Tested: P3AS05R209024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246047
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 170.0 lumens
Efficiency: N/A
Efficacy: 23.6 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246047

CATALOG NUMBER: P3AS05R209024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246047

CATALOG NUMBER: P3AS05R209024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42058
5°	40920
10°	37652
15°	33144
20°	28422
25°	23880
30°	19294
35°	14696
40°	10448
45°	6884
50°	4264
55°	2791
60°	2544
65°	2335
70°	2244
75°	2033
80°	1894
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6884 cd/sqm

TEST NUMBER: P1246047

CATALOG NUMBER: P3AS05R209024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.2	10.1
10°-20°	40.6	23.9
20°-30°	45.1	26.5
30°-40°	34.4	20.3
40°-50°	17.6	10.4
50°-60°	7.2	4.3
60°-70°	4.5	2.7
70°-80°	2.5	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.0	60.6
0°-40°	137.4	80.8
0°-60°	162.2	95.4
0°-90°	170.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	170.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	192	
5°	186	17
15°	146	41
25°	99	45
35°	55	34
45°	22	18
55°	7	7
65°	4	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1246047

CATALOG NUMBER: P3AS05R209024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	191.8
1°	192.0
2°	191.1
3°	190.0
4°	188.3
5°	185.9
6°	183.1
7°	180.1
8°	176.9
9°	173.0
10°	169.1
12.5°	157.9
15°	146.0
17.5°	133.9
20°	121.8
22.5°	109.7
25°	98.7
27.5°	87.7
30°	76.2
32.5°	65.4
35°	54.9
37.5°	45.6
40°	36.5
42.5°	28.7
45°	22.2
47.5°	16.8
50°	12.5
52.5°	9.3
55°	7.3
57.5°	6.7
60°	5.8
62.5°	5.2
65°	4.5
67.5°	3.9
70°	3.5
72.5°	2.8
75°	2.4
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)