

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247380

Luminaire Tested: P3AS17R509024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1577.1 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247380

CATALOG NUMBER: P3AS17R509024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247380

CATALOG NUMBER: P3AS17R509024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	551096
5°	536428
10°	511903
15°	463431
20°	400925
25°	328882
30°	188915
35°	58678
40°	15772
45°	5520
50°	1330
55°	421
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5520 cd/sqm

TEST NUMBER: P1247380

CATALOG NUMBER: P3AS17R509024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.3	14.5
10°-20°	565.6	35.9
20°-30°	594.5	37.7
30°-40°	170.2	10.8
40°-50°	16.6	1.1
50°-60°	1.4	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1388.4	88.0
0°-40°	1558.6	98.8
0°-60°	1576.5	100.0
0°-90°	1577.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1577.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2513	
5°	2437	228
15°	2041	566
25°	1359	595
35°	219	170
45°	18	17
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247380

CATALOG NUMBER: P3AS17R509024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2513.2
1°	2509.3
2°	2498.2
3°	2482.1
4°	2460.4
5°	2437.0
6°	2411.9
7°	2385.2
8°	2360.2
9°	2331.3
10°	2299.0
11°	2261.7
12°	2218.9
13°	2165.5
14°	2107.6
15°	2041.4
16°	1971.3
17°	1903.4
18°	1833.9
19°	1772.7
20°	1718.1
21°	1665.8
22°	1606.3
23°	1537.9
24°	1457.7
25°	1359.3
26°	1252.4
27°	1133.4
28°	1014.9
29°	886.9
30°	746.1
31°	614.3
32°	493.0
32.5°	440.1
33°	386.7
34°	296.6
35°	219.2
36°	160.8
37°	119.6
37.5°	103.5
38°	89.6
39°	69.5
40°	55.1
42.5°	31.2
45°	17.8

TEST NUMBER: P1247380

CATALOG NUMBER: P3AS17R509024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	10.0
50°	3.9
52.5°	1.7
55°	1.1
57.5°	1.1
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)