

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247395

Luminaire Tested: P3AS17R509024DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509024DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 839.0 lumens
Efficiency: N/A
Efficacy: 39.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247395
CATALOG NUMBER: P3AS17R509024DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1247395
 CATALOG NUMBER: P3AS17R509024DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244016
5°	237464
10°	218967
15°	192555
20°	161107
25°	127749
30°	93736
35°	64434
40°	40962
45°	22886
50°	12383
55°	10437
60°	8947
65°	8250
70°	7309
75°	6693
80°	5683
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22886 cd/sqm



TEST NUMBER: P1247395
 CATALOG NUMBER: P3AS17R509024DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	11.9
10°-20°	234.9	28.0
20°-30°	240.3	28.6
30°-40°	152.4	18.2
40°-50°	60.6	7.2
50°-60°	24.6	2.9
60°-70°	15.7	1.9
70°-80°	8.1	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.1	68.6
0°-40°	727.5	86.7
0°-60°	812.7	96.9
0°-90°	839.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	839.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1113	
5°	1079	100
15°	848	235
25°	528	240
35°	241	152
45°	74	61
55°	27	25
65°	16	16
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1247395
CATALOG NUMBER: P3AS17R509024DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1112.8
2.5°	1104.9
5°	1078.8
7.5°	1037.9
10°	983.4
12.5°	918.6
15°	848.2
17.5°	771.0
20°	690.4
22.5°	609.8
25°	528.0
27.5°	446.3
30°	370.2
32.5°	302.1
35°	240.7
37.5°	188.5
40°	143.1
42.5°	105.6
45°	73.8
47.5°	50.0
50°	36.3
52.5°	30.7
55°	27.3
57.5°	23.8
60°	20.4
62.5°	18.2
65°	15.9
67.5°	13.6
70°	11.4
72.5°	9.1
75°	7.9
77.5°	5.7
80°	4.5
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0

(END OF REPORT)