

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247400

Luminaire Tested: P3AS17R559024DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559024DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1511.0 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247400
CATALOG NUMBER: P3AS17R559024DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1247400
 CATALOG NUMBER: P3AS17R559024DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94	94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89	89	89	89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84	84	84	84
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79	79	79	79
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74	74	74	74
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70	70	70	70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66	66	66	66
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63	63	63	63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60	60	60	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419089
5°	415187
10°	431878
15°	425882
20°	392711
25°	319543
30°	194080
35°	67191
40°	19179
45°	9148
50°	3889
55°	1720
60°	1974
65°	1764
70°	1475
75°	1949
80°	1389
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9148 cd/sqm



TEST NUMBER: P1247400
 CATALOG NUMBER: P3AS17R559024DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.3	12.1
10°-20°	521.4	34.5
20°-30°	581.3	38.5
30°-40°	190.2	12.6
40°-50°	25.1	1.7
50°-60°	5.3	0.3
60°-70°	3.1	0.2
70°-80°	2.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1285.0	85.0
0°-40°	1475.1	97.6
0°-60°	1505.5	99.6
0°-90°	1511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1511.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1911	
5°	1886	182
15°	1876	521
25°	1321	581
35°	251	190
45°	30	25
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1247400
CATALOG NUMBER: P3AS17R559024DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1911.2
2.5°	1897.5
5°	1886.2
7.5°	1913.4
10°	1939.6
12.5°	1925.9
15°	1876.0
17.5°	1796.5
20°	1682.9
22.5°	1526.2
25°	1320.7
27.5°	1059.5
30°	766.5
32.5°	470.1
35°	251.0
37.5°	127.2
40°	67.0
42.5°	43.2
45°	29.5
47.5°	20.4
50°	11.4
52.5°	6.8
55°	4.5
57.5°	4.5
60°	4.5
62.5°	3.4
65°	3.4
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)