

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247416

Luminaire Tested: P3AS17R559024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 471.0 lumens
Efficiency: N/A
Efficacy: 22.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247416
CATALOG NUMBER: P3AS17R559024DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247416
 CATALOG NUMBER: P3AS17R559024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	54	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88567
5°	87431
10°	83989
15°	78548
20°	71663
25°	63923
30°	55907
35°	46471
40°	36611
45°	24840
50°	15181
55°	7875
60°	7324
65°	6953
70°	6411
75°	5676
80°	5683
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24840 cd/sqm



TEST NUMBER: P1247416
 CATALOG NUMBER: P3AS17R559024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.3	7.9
10°-20°	96.7	20.5
20°-30°	121.1	25.7
30°-40°	108.1	23.0
40°-50°	63.3	13.4
50°-60°	21.9	4.6
60°-70°	13.2	2.8
70°-80°	7.3	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.1	54.1
0°-40°	363.2	77.1
0°-60°	448.3	95.2
0°-90°	471.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	471.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	404	
5°	397	37
15°	346	97
25°	264	121
35°	174	108
45°	80	63
55°	21	22
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1247416
CATALOG NUMBER: P3AS17R559024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	403.9
2.5°	401.6
5°	397.2
7.5°	388.3
10°	377.2
12.5°	363.3
15°	346.0
17.5°	327.7
20°	307.1
22.5°	285.9
25°	264.2
27.5°	242.5
30°	220.8
32.5°	197.5
35°	173.6
37.5°	150.2
40°	127.9
42.5°	104.0
45°	80.1
47.5°	61.2
50°	44.5
52.5°	28.9
55°	20.6
57.5°	18.4
60°	16.7
62.5°	15.0
65°	13.4
67.5°	11.7
70°	10.0
72.5°	8.3
75°	6.7
77.5°	5.6
80°	4.5
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

(END OF REPORT)