

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246110

Luminaire Tested: P3AS05R309024DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309024DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 360.0 lumens
Efficiency: N/A
Efficacy: 50.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246110
CATALOG NUMBER: P3AS05R309024DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1246110
 CATALOG NUMBER: P3AS05R309024DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85059
5°	83139
10°	77309
15°	68786
20°	59178
25°	50132
30°	41601
35°	32632
40°	23387
45°	15350
50°	8733
55°	5735
60°	5438
65°	5033
70°	4552
75°	4151
80°	3915
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15350 cd/sqm



TEST NUMBER: P1246110
 CATALOG NUMBER: P3AS05R309024DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.1	9.7
10°-20°	84.2	23.4
20°-30°	94.9	26.4
30°-40°	75.8	21.1
40°-50°	39.0	10.8
50°-60°	14.7	4.1
60°-70°	9.6	2.7
70°-80°	5.2	1.4
80°-90°	1.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	214.3	59.5
0°-40°	290.1	80.6
0°-60°	343.7	95.5
0°-90°	360.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	360.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	388	
5°	378	35
15°	303	84
25°	207	95
35°	122	76
45°	50	39
55°	15	15
65°	10	10
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1246110
CATALOG NUMBER: P3AS05R309024DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	387.9
1°	387.9
2°	386.5
3°	384.3
4°	381.2
5°	377.7
6°	373.3
7°	367.5
8°	361.4
9°	354.3
10°	347.2
11°	339.3
12°	330.9
13°	322.0
14°	312.8
15°	303.0
17.5°	278.3
20°	253.6
22.5°	229.7
25°	207.2
27.5°	185.1
30°	164.3
32.5°	143.1
35°	121.9
37.5°	101.2
40°	81.7
42.5°	64.5
45°	49.5
47.5°	36.7
50°	25.6
52.5°	18.1
55°	15.0
57.5°	13.7
60°	12.4
62.5°	11.0
65°	9.7
67.5°	8.4
70°	7.1
72.5°	5.7
75°	4.9
77.5°	4.0
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.4



TEST NUMBER: P1246110
CATALOG NUMBER: P3AS05R309024DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)