

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247450

Luminaire Tested: P3AS17R609024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 936.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247450

CATALOG NUMBER: P3AS17R609024DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247450

CATALOG NUMBER: P3AS17R609024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166149
5°	164296
10°	158603
15°	149831
20°	138122
25°	125064
30°	111030
35°	94870
40°	75456
45°	53184
50°	31794
55°	16057
60°	15437
65°	14165
70°	13079
75°	12539
80°	11491
85°	8554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 53184 cd/sqm

TEST NUMBER: P1247450

CATALOG NUMBER: P3AS17R609024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.1	7.5
10°-20°	184.5	19.7
20°-30°	236.9	25.3
30°-40°	219.6	23.5
40°-50°	133.7	14.3
50°-60°	44.5	4.8
60°-70°	27.1	2.9
70°-80°	15.3	1.6
80°-90°	4.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.5	52.5
0°-40°	711.0	76.0
0°-60°	889.3	95.0
0°-90°	936.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	936.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	758	
5°	746	70
15°	660	184
25°	517	237
35°	354	220
45°	172	134
55°	42	45
65°	27	27
75°	15	15
85°	3	4
90°	0	

TEST NUMBER: P1247450

CATALOG NUMBER: P3AS17R609024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	757.7
2.5°	754.3
5°	746.4
7.5°	731.6
10°	712.3
12.5°	688.4
15°	660.0
17.5°	627.1
20°	591.9
22.5°	554.4
25°	516.9
27.5°	478.3
30°	438.5
32.5°	398.7
35°	354.4
37.5°	307.9
40°	263.6
42.5°	217.0
45°	171.5
47.5°	132.9
50°	93.2
52.5°	55.7
55°	42.0
57.5°	38.6
60°	35.2
62.5°	30.7
65°	27.3
67.5°	23.9
70°	20.4
72.5°	17.0
75°	14.8
77.5°	11.4
80°	9.1
82.5°	5.7
85°	3.4
87.5°	2.3
90°	0.0

(END OF REPORT)