

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246141

Luminaire Tested: P3AS05R359024DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246141  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R359024DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 286.0 lumens  
Efficiency: N/A  
Efficacy: 39.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246141  
CATALOG NUMBER: P3AS05R359024DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1246141  
 CATALOG NUMBER: P3AS05R359024DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80				80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69				69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57				57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91922
5°	89654
10°	81962
15°	69580
20°	55071
25°	41664
30°	30334
35°	20505
40°	12595
45°	7226
50°	4367
55°	3517
60°	3070
65°	2750
70°	2244
75°	2203
80°	2273
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7226 cd/sqm



TEST NUMBER: P1246141  
 CATALOG NUMBER: P3AS05R359024DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.6	13.2
10°-20°	84.5	29.5
20°-30°	79.0	27.6
30°-40°	48.4	16.9
40°-50°	19.1	6.7
50°-60°	8.4	2.9
60°-70°	5.2	1.8
70°-80°	2.8	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	201.2	70.4
0°-40°	249.6	87.3
0°-60°	277.0	96.9
0°-90°	286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	286.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	419	
5°	407	38
15°	306	84
25°	172	79
35°	77	48
45°	23	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1246141  
CATALOG NUMBER: P3AS05R359024DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	419.2
1°	419.7
2°	418.3
3°	415.7
4°	411.7
5°	407.3
6°	401.6
7°	395.0
8°	387.1
9°	378.3
10°	368.1
11°	357.6
12°	346.1
13°	333.8
14°	320.1
15°	306.5
17.5°	271.3
20°	236.0
22.5°	202.1
25°	172.2
27.5°	144.4
30°	119.8
32.5°	96.9
35°	76.6
37.5°	58.6
40°	44.0
42.5°	31.7
45°	23.3
47.5°	16.7
50°	12.8
52.5°	10.6
55°	9.2
57.5°	7.9
60°	7.0
62.5°	6.2
65°	5.3
67.5°	4.4
70°	3.5
72.5°	3.1
75°	2.6
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4



TEST NUMBER: P1246141  
CATALOG NUMBER: P3AS05R359024DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)