

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247468

Luminaire Tested: P3AS17R659024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 558.0 lumens
Efficiency: N/A
Efficacy: 26.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247468

CATALOG NUMBER: P3AS17R659024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1247468

CATALOG NUMBER: P3AS17R659024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131590
5°	130024
10°	125070
15°	117163
20°	105382
25°	89497
30°	69985
35°	49871
40°	32633
45°	20188
50°	10234
55°	3632
60°	3158
65°	3165
70°	2821
75°	2796
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20188 cd/sqm

TEST NUMBER: P1247468

CATALOG NUMBER: P3AS17R659024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.5	9.9
10°-20°	143.6	25.7
20°-30°	167.9	30.1
30°-40°	117.3	21.0
40°-50°	51.6	9.3
50°-60°	11.5	2.1
60°-70°	5.8	1.0
70°-80°	3.5	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	367.0	65.8
0°-40°	484.3	86.8
0°-60°	547.4	98.1
0°-90°	558.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	600	
5°	591	55
15°	516	144
25°	370	168
35°	186	117
45°	65	52
55°	10	11
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1247468

CATALOG NUMBER: P3AS17R659024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	600.1
2.5°	597.9
5°	590.7
7.5°	578.4
10°	561.7
12.5°	541.2
15°	516.1
17.5°	485.5
20°	451.6
22.5°	413.2
25°	369.9
27.5°	324.2
30°	276.4
32.5°	230.3
35°	186.3
37.5°	147.9
40°	114.0
42.5°	86.2
45°	65.1
47.5°	47.8
50°	30.0
52.5°	15.6
55°	9.5
57.5°	8.3
60°	7.2
62.5°	6.7
65°	6.1
67.5°	5.0
70°	4.4
72.5°	3.9
75°	3.3
77.5°	2.8
80°	2.2
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)