

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246159

Luminaire Tested: P3AS05R409024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 618.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246159

CATALOG NUMBER: P3AS05R409024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246159

CATALOG NUMBER: P3AS05R409024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	109		112	110	109	107		106	105	104		103	102	101		99	98	98
2	111	107	104	101		109	105	102	100		102	100	98		99	97	96		96	95	94
3	107	102	98	95		105	100	97	94		98	95	93		96	93	91		93	91	90
4	103	97	93	90		101	96	92	89		94	91	88		92	89	87		90	88	86
5	99	93	89	85		98	92	88	85		91	87	84		89	86	84		88	85	83
6	96	89	85	81		95	89	84	81		87	83	81		86	83	80		85	82	80
7	93	86	81	78		92	85	81	78		84	80	77		83	80	77		82	79	77
8	90	83	78	75		89	82	78	75		81	77	75		80	77	74		79	76	74
9	87	80	75	72		86	79	75	72		78	75	72		78	74	72		77	74	71
10	84	77	72	70		83	77	72	69		76	72	69		75	72	69		75	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315019
5°	312744
10°	304559
15°	272056
20°	180382
25°	67576
30°	18079
35°	7067
40°	2548
45°	1209
50°	375
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1209 cd/sqm

TEST NUMBER: P1246159

CATALOG NUMBER: P3AS05R409024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	21.7
10°-20°	317.5	51.4
20°-30°	144.0	23.3
30°-40°	18.7	3.0
40°-50°	3.2	0.5
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.6	96.4
0°-40°	614.3	99.4
0°-60°	617.9	100.0
0°-90°	618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	618.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1437	
5°	1421	134
15°	1198	318
25°	279	144
35°	26	19
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246159

CATALOG NUMBER: P3AS05R409024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1436.6
1°	1435.7
2°	1433.5
3°	1430.3
4°	1426.2
5°	1420.8
6°	1414.5
7°	1406.7
8°	1397.2
9°	1384.2
10°	1367.8
11°	1348.5
12°	1322.8
13°	1291.0
14°	1249.4
15°	1198.4
16°	1133.2
17°	1059.0
18°	969.9
19°	875.8
20°	773.0
21°	670.2
22°	569.0
23°	468.2
24°	369.1
25°	279.3
26°	206.8
27°	151.4
28°	113.8
29°	88.5
30°	71.4
31°	59.1
32°	49.3
32.5°	45.0
33°	40.7
34°	33.1
35°	26.4
36°	20.8
37°	16.4
37.5°	14.7
38°	13.0
39°	10.8
40°	8.9
42.5°	5.8
45°	3.9



TEST NUMBER: P1246159

CATALOG NUMBER: P3AS05R409024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.4
50°	1.1
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)