

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247474

Luminaire Tested: P3AS17R659024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 438.0 lumens
Efficiency: N/A
Efficacy: 20.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247474
CATALOG NUMBER: P3AS17R659024DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247474
 CATALOG NUMBER: P3AS17R659024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91				91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82				82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61				61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47				47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44				44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77954
5°	76887
10°	74325
15°	70080
20°	64639
25°	58673
30°	51983
35°	44223
40°	35180
45°	24840
50°	14430
55°	7875
60°	7324
65°	6641
70°	6091
75°	5676
80°	4925
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24840 cd/sqm



TEST NUMBER: P1247474
 CATALOG NUMBER: P3AS17R659024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.9	7.5
10°-20°	86.4	19.7
20°-30°	111.0	25.3
30°-40°	102.7	23.4
40°-50°	62.0	14.1
50°-60°	21.2	4.8
60°-70°	12.7	2.9
70°-80°	7.2	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.2	52.6
0°-40°	332.9	76.0
0°-60°	416.0	95.0
0°-90°	438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	438.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	356	
5°	349	33
15°	309	86
25°	242	111
35°	165	103
45°	80	62
55°	21	21
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1247474
CATALOG NUMBER: P3AS17R659024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	355.5
2.5°	353.8
5°	349.3
7.5°	342.7
10°	333.8
12.5°	322.6
15°	308.7
17.5°	293.7
20°	277.0
22.5°	259.8
25°	242.5
27.5°	224.2
30°	205.3
32.5°	186.3
35°	165.2
37.5°	144.6
40°	122.9
42.5°	101.2
45°	80.1
47.5°	60.6
50°	42.3
52.5°	26.7
55°	20.6
57.5°	18.4
60°	16.7
62.5°	14.5
65°	12.8
67.5°	11.1
70°	9.5
72.5°	8.3
75°	6.7
77.5°	5.6
80°	3.9
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

(END OF REPORT)