

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246166

Luminaire Tested: P3AS05R409024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 192.9 lumens
Efficiency: N/A
Efficacy: 26.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246166

CATALOG NUMBER: P3AS05R409024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246166

CATALOG NUMBER: P3AS05R409024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43330
5°	42549
10°	40102
15°	36413
20°	31993
25°	27316
30°	22636
35°	17454
40°	12423
45°	8373
50°	4571
55°	3211
60°	3026
65°	2802
70°	2500
75°	2372
80°	1894
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8373 cd/sqm

TEST NUMBER: P1246166

CATALOG NUMBER: P3AS05R409024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.0	9.3
10°-20°	44.7	23.2
20°-30°	51.7	26.8
30°-40°	40.7	21.1
40°-50°	20.9	10.8
50°-60°	8.0	4.1
60°-70°	5.3	2.7
70°-80°	2.9	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	114.4	59.3
0°-40°	155.1	80.4
0°-60°	184.0	95.4
0°-90°	192.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	192.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	198	
5°	193	18
15°	160	45
25°	113	52
35°	65	41
45°	27	21
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246166

CATALOG NUMBER: P3AS05R409024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	197.6
2.5°	196.5
5°	193.3
7.5°	187.6
10°	180.1
12.5°	171.2
15°	160.4
17.5°	149.2
20°	137.1
22.5°	124.8
25°	112.9
27.5°	101.1
30°	89.4
32.5°	77.5
35°	65.2
37.5°	53.8
40°	43.4
42.5°	34.5
45°	27.0
47.5°	19.6
50°	13.4
52.5°	9.7
55°	8.4
57.5°	7.6
60°	6.9
62.5°	6.0
65°	5.4
67.5°	4.5
70°	3.9
72.5°	3.2
75°	2.8
77.5°	2.2
80°	1.5
82.5°	1.3
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)