

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247501

Luminaire Tested: P3AS17R709024DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247501
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709024DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 816.0 lumens
Efficiency: N/A
Efficacy: 38.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247501
CATALOG NUMBER: P3AS17R709024DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1247501
 CATALOG NUMBER: P3AS17R709024DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191410
5°	187893
10°	177173
15°	160795
20°	140642
25°	118628
30°	97154
35°	75355
40°	53930
45°	34143
50°	17023
55°	10399
60°	8947
65°	8250
70°	7309
75°	6693
80°	5683
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34143 cd/sqm



TEST NUMBER: P1247501
 CATALOG NUMBER: P3AS17R709024DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	9.8
10°-20°	197.1	24.2
20°-30°	224.5	27.5
30°-40°	175.5	21.5
40°-50°	86.2	10.6
50°-60°	26.5	3.2
60°-70°	15.7	1.9
70°-80°	8.4	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.2	61.4
0°-40°	676.7	82.9
0°-60°	789.4	96.7
0°-90°	816.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	873	
5°	854	80
15°	708	197
25°	490	224
35°	282	176
45°	110	86
55°	27	26
65°	16	16
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1247501
CATALOG NUMBER: P3AS17R709024DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	872.9
2.5°	868.3
5°	853.6
7.5°	829.7
10°	795.7
12.5°	756.0
15°	708.3
17.5°	657.2
20°	602.7
22.5°	546.0
25°	490.3
27.5°	435.9
30°	383.7
32.5°	331.4
35°	281.5
37.5°	233.8
40°	188.4
42.5°	146.4
45°	110.1
47.5°	77.2
50°	49.9
52.5°	32.9
55°	27.2
57.5°	23.8
60°	20.4
62.5°	18.2
65°	15.9
67.5°	13.6
70°	11.4
72.5°	9.1
75°	7.9
77.5°	6.8
80°	4.5
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0

(END OF REPORT)