

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246225

Luminaire Tested: P3AS05R509024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 387.0 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246225

CATALOG NUMBER: P3AS05R509024DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246225

CATALOG NUMBER: P3AS05R509024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78656
5°	77482
10°	74058
15°	68582
20°	61629
25°	54172
30°	46083
35°	37370
40°	28081
45°	18079
50°	8597
55°	6767
60°	6403
65°	5967
70°	5386
75°	4829
80°	4420
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18079 cd/sqm

TEST NUMBER: P1246225

CATALOG NUMBER: P3AS05R509024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.0	8.5
10°-20°	84.2	21.8
20°-30°	102.3	26.4
30°-40°	86.8	22.4
40°-50°	45.1	11.7
50°-60°	16.3	4.2
60°-70°	11.3	2.9
70°-80°	6.1	1.6
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	219.6	56.7
0°-40°	306.4	79.2
0°-60°	367.7	95.0
0°-90°	387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	387.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	359	
5°	352	33
15°	302	84
25°	224	102
35°	140	87
45°	58	45
55°	18	16
65°	12	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1246225

CATALOG NUMBER: P3AS05R509024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	358.7
2.5°	357.3
5°	352.0
7.5°	344.1
10°	332.6
12.5°	318.0
15°	302.1
17.5°	284.0
20°	264.1
22.5°	243.8
25°	223.9
27.5°	203.2
30°	182.0
32.5°	160.8
35°	139.6
37.5°	118.8
40°	98.1
42.5°	78.2
45°	58.3
47.5°	38.9
50°	25.2
52.5°	19.4
55°	17.7
57.5°	15.9
60°	14.6
62.5°	12.8
65°	11.5
67.5°	9.7
70°	8.4
72.5°	7.1
75°	5.7
77.5°	4.4
80°	3.5
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)