

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246263

Luminaire Tested: P3AS05R609024DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609024DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 571.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246263

CATALOG NUMBER: P3AS05R609024DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1246263

CATALOG NUMBER: P3AS05R609024DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		79	70	64	60		69	64	60		68	63	60		67	63	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136349
5°	130948
10°	134823
15°	136550
20°	120574
25°	101619
30°	82418
35°	53672
40°	24646
45°	9458
50°	3173
55°	841
60°	789
65°	675
70°	577
75°	763
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9458 cd/sqm

TEST NUMBER: P1246263

CATALOG NUMBER: P3AS05R609024DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.3	10.0
10°-20°	164.7	28.8
20°-30°	192.1	33.6
30°-40°	124.0	21.7
40°-50°	27.8	4.9
50°-60°	2.8	0.5
60°-70°	1.3	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.1	72.5
0°-40°	538.1	94.2
0°-60°	568.7	99.6
0°-90°	571.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	571.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	622	
5°	595	57
15°	602	165
25°	420	192
35°	200	124
45°	30	28
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246263

CATALOG NUMBER: P3AS05R609024DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	621.8
2.5°	611.7
5°	594.9
7.5°	594.0
10°	605.5
12.5°	613.0
15°	601.5
17.5°	567.1
20°	516.7
22.5°	464.2
25°	420.0
27.5°	376.7
30°	325.5
32.5°	265.4
35°	200.5
37.5°	136.9
40°	86.1
42.5°	51.7
45°	30.5
47.5°	17.7
50°	9.3
52.5°	3.1
55°	2.2
57.5°	1.8
60°	1.8
62.5°	1.3
65°	1.3
67.5°	1.3
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)