

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246272

Luminaire Tested: P3AS05R609024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 228.0 lumens
Efficiency: N/A
Efficacy: 31.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246272

CATALOG NUMBER: P3AS05R609024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246272

CATALOG NUMBER: P3AS05R609024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		67
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53833
5°	53335
10°	51769
15°	48513
20°	42937
25°	35905
30°	28156
35°	20425
40°	13597
45°	8466
50°	4571
55°	1338
60°	1228
65°	1141
70°	1090
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8466 cd/sqm

TEST NUMBER: P1246272

CATALOG NUMBER: P3AS05R609024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.8	10.0
10°-20°	59.3	26.0
20°-30°	67.6	29.6
30°-40°	47.9	21.0
40°-50°	21.8	9.5
50°-60°	4.6	2.0
60°-70°	2.2	1.0
70°-80°	1.4	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.7	65.6
0°-40°	197.6	86.6
0°-60°	223.9	98.2
0°-90°	228.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	228.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	246	
5°	242	23
15°	214	59
25°	148	68
35°	76	48
45°	27	22
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246272

CATALOG NUMBER: P3AS05R609024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	245.5
2.5°	244.7
5°	242.3
7.5°	238.2
10°	232.5
12.5°	224.5
15°	213.7
17.5°	200.0
20°	184.0
22.5°	166.6
25°	148.4
27.5°	129.8
30°	111.2
32.5°	93.4
35°	76.3
37.5°	61.1
40°	47.5
42.5°	36.0
45°	27.3
47.5°	20.4
50°	13.4
52.5°	6.3
55°	3.5
57.5°	3.0
60°	2.8
62.5°	2.6
65°	2.2
67.5°	2.0
70°	1.7
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)