

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246277

Luminaire Tested: P3AS05R609024DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609024DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 465.0 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246277

CATALOG NUMBER: P3AS05R609024DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246277

CATALOG NUMBER: P3AS05R609024DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109794
5°	108760
10°	105587
15°	98934
20°	87554
25°	73238
30°	57401
35°	41653
40°	27709
45°	17273
50°	9347
55°	2714
60°	2500
65°	2283
70°	2244
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 17273 cd/sqm

TEST NUMBER: P1246277

CATALOG NUMBER: P3AS05R609024DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	10.0
10°-20°	120.9	26.0
20°-30°	137.8	29.6
30°-40°	97.7	21.0
40°-50°	44.3	9.5
50°-60°	9.4	2.0
60°-70°	4.5	1.0
70°-80°	2.8	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	305.2	65.6
0°-40°	402.9	86.7
0°-60°	456.7	98.2
0°-90°	465.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	501	
5°	494	47
15°	436	121
25°	303	138
35°	156	98
45°	56	44
55°	7	9
65°	4	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246277

CATALOG NUMBER: P3AS05R609024DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	500.7
2.5°	499.0
5°	494.1
7.5°	485.7
10°	474.2
12.5°	457.9
15°	435.8
17.5°	407.9
20°	375.2
22.5°	339.9
25°	302.7
27.5°	264.7
30°	226.7
32.5°	190.5
35°	155.6
37.5°	124.6
40°	96.8
42.5°	73.4
45°	55.7
47.5°	41.5
50°	27.4
52.5°	12.8
55°	7.1
57.5°	6.2
60°	5.7
62.5°	5.3
65°	4.4
67.5°	4.0
70°	3.5
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)