

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246284

Luminaire Tested: P3AS05R609024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 157.0 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246284

CATALOG NUMBER: P3AS05R609024DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246284

CATALOG NUMBER: P3AS05R609024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39799
5°	38895
10°	36405
15°	32668
20°	28096
25°	23227
30°	18357
35°	13626
40°	9389
45°	5892
50°	3241
55°	1912
60°	1710
65°	1453
70°	1218
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5892 cd/sqm

TEST NUMBER: P1246284

CATALOG NUMBER: P3AS05R609024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.5	10.5
10°-20°	40.0	25.5
20°-30°	43.8	27.9
30°-40°	31.9	20.3
40°-50°	15.1	9.6
50°-60°	5.0	3.2
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	100.3	63.9
0°-40°	132.2	84.2
0°-60°	152.2	97.0
0°-90°	157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	182	
5°	177	16
15°	144	40
25°	96	44
35°	51	32
45°	19	15
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1246284

CATALOG NUMBER: P3AS05R609024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	181.5
2.5°	180.4
5°	176.7
7.5°	171.1
10°	163.5
12.5°	154.5
15°	143.9
17.5°	132.5
20°	120.4
22.5°	108.1
25°	96.0
27.5°	83.9
30°	72.5
32.5°	61.5
35°	50.9
37.5°	41.4
40°	32.8
42.5°	25.2
45°	19.0
47.5°	13.8
50°	9.5
52.5°	6.3
55°	5.0
57.5°	4.3
60°	3.9
62.5°	3.2
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.5
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)