

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246293

Luminaire Tested: P3AS05R659024DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659024DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 546.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246293

CATALOG NUMBER: P3AS05R659024DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1246293

CATALOG NUMBER: P3AS05R659024DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133432
5°	125577
10°	123979
15°	121794
20°	114997
25°	106724
30°	82949
35°	47997
40°	19351
45°	8900
50°	3480
55°	1338
60°	1140
65°	1141
70°	1154
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8900 cd/sqm

TEST NUMBER: P1246293

CATALOG NUMBER: P3AS05R659024DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	9.9
10°-20°	149.8	27.4
20°-30°	196.1	35.9
30°-40°	113.6	20.8
40°-50°	24.3	4.5
50°-60°	4.0	0.7
60°-70°	2.2	0.4
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	400.2	73.3
0°-40°	513.8	94.1
0°-60°	542.0	99.3
0°-90°	546.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	546.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	608	
5°	570	54
15°	536	150
25°	441	196
35°	179	114
45°	29	24
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246293

CATALOG NUMBER: P3AS05R659024DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	608.5
2.5°	591.3
5°	570.5
7.5°	562.1
10°	556.8
12.5°	549.3
15°	536.5
17.5°	516.6
20°	492.8
22.5°	470.3
25°	441.1
27.5°	392.1
30°	327.6
32.5°	253.9
35°	179.3
37.5°	113.5
40°	67.6
42.5°	42.4
45°	28.7
47.5°	18.5
50°	10.2
52.5°	4.9
55°	3.5
57.5°	3.1
60°	2.6
62.5°	2.6
65°	2.2
67.5°	1.8
70°	1.8
72.5°	1.3
75°	1.3
77.5°	0.9
80°	0.9
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)