

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246330

Luminaire Tested: P3AS05R709024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 218.0 lumens
Efficiency: N/A
Efficacy: 30.3 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246330

CATALOG NUMBER: P3AS05R709024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246330

CATALOG NUMBER: P3AS05R709024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77		
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70		
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42212
5°	41690
10°	40502
15°	38774
20°	36333
25°	33002
30°	28511
35°	22727
40°	16545
45°	10885
50°	5083
55°	1567
60°	1535
65°	1453
70°	1410
75°	1440
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10885 cd/sqm

TEST NUMBER: P1246330

CATALOG NUMBER: P3AS05R709024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.8	8.2
10°-20°	47.8	21.9
20°-30°	62.1	28.5
30°-40°	52.7	24.2
40°-50°	27.2	12.5
50°-60°	5.2	2.4
60°-70°	2.8	1.3
70°-80°	1.7	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	127.8	58.6
0°-40°	180.5	82.8
0°-60°	212.9	97.7
0°-90°	218.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	218.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	192	
5°	189	18
15°	171	48
25°	136	62
35°	85	53
45°	35	27
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1246330

CATALOG NUMBER: P3AS05R709024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	192.5
2.5°	191.8
5°	189.4
7.5°	186.0
10°	181.9
12.5°	176.7
15°	170.8
17.5°	163.7
20°	155.7
22.5°	146.6
25°	136.4
27.5°	124.9
30°	112.6
32.5°	98.9
35°	84.9
37.5°	71.0
40°	57.8
42.5°	45.5
45°	35.1
47.5°	25.8
50°	14.9
52.5°	6.5
55°	4.1
57.5°	3.9
60°	3.5
62.5°	3.2
65°	2.8
67.5°	2.6
70°	2.2
72.5°	1.9
75°	1.7
77.5°	1.3
80°	1.1
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)