

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247654

Luminaire Tested: P3AS20R359024D010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1247654  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R359024D010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 967.0 lumens  
Efficiency: N/A  
Efficacy: 33.6 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247654

CATALOG NUMBER: P3AS20R359024D010 E3DLP1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1247654

CATALOG NUMBER: P3AS20R359024D010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 97  | 93  | 97  | 94  | 91  |  | 94  | 92  | 89  |  | 91  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 85  | 82  |  | 86  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 82  | 78  | 86  | 81  | 77  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 7   | 83  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 69  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 63  | 59  | 68  | 63  | 59  |  | 67  | 62  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 61  | 56  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 310830 |
| 5°  | 303169 |
| 10° | 277149 |
| 15° | 235257 |
| 20° | 186240 |
| 25° | 140863 |
| 30° | 102547 |
| 35° | 69359  |
| 40° | 42623  |
| 45° | 24468  |
| 50° | 14737  |
| 55° | 11966  |
| 60° | 10438  |
| 65° | 9288   |
| 70° | 7629   |
| 75° | 7540   |
| 80° | 7577   |
| 85° | 7548   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24468 cd/sqm

TEST NUMBER: P1247654

CATALOG NUMBER: P3AS20R359024D010 E3DLP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 127.3  | 13.2      |
| 10°-20°   | 285.7  | 29.5      |
| 20°-30°   | 267.3  | 27.6      |
| 30°-40°   | 163.6  | 16.9      |
| 40°-50°   | 64.5   | 6.7       |
| 50°-60°   | 28.4   | 2.9       |
| 60°-70°   | 17.7   | 1.8       |
| 70°-80°   | 9.4    | 1.0       |
| 80°-90°   | 3.3    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 680.2  | 70.3      |
| 0°-40°    | 843.8  | 87.3      |
| 0°-60°    | 936.7  | 96.9      |
| 0°-90°    | 967.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 967.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1418 |      |
| 5°  | 1377 | 127  |
| 15° | 1036 | 286  |
| 25° | 582  | 267  |
| 35° | 259  | 164  |
| 45° | 79   | 64   |
| 55° | 31   | 28   |
| 65° | 18   | 18   |
| 75° | 9    | 9    |
| 85° | 3    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1247654

CATALOG NUMBER: P3AS20R359024D010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1417.5 |
| 1°    | 1418.9 |
| 2°    | 1414.5 |
| 3°    | 1405.5 |
| 4°    | 1392.1 |
| 5°    | 1377.3 |
| 6°    | 1357.9 |
| 7°    | 1335.6 |
| 8°    | 1308.8 |
| 9°    | 1279.0 |
| 10°   | 1244.7 |
| 11°   | 1209.0 |
| 12°   | 1170.3 |
| 13°   | 1128.6 |
| 14°   | 1082.4 |
| 15°   | 1036.3 |
| 17.5° | 917.2  |
| 20°   | 798.1  |
| 22.5° | 683.4  |
| 25°   | 582.2  |
| 27.5° | 488.4  |
| 30°   | 405.0  |
| 32.5° | 327.6  |
| 35°   | 259.1  |
| 37.5° | 198.0  |
| 40°   | 148.9  |
| 42.5° | 107.2  |
| 45°   | 78.9   |
| 47.5° | 56.6   |
| 50°   | 43.2   |
| 52.5° | 35.7   |
| 55°   | 31.3   |
| 57.5° | 26.8   |
| 60°   | 23.8   |
| 62.5° | 20.8   |
| 65°   | 17.9   |
| 67.5° | 14.9   |
| 70°   | 11.9   |
| 72.5° | 10.4   |
| 75°   | 8.9    |
| 77.5° | 7.4    |
| 80°   | 6.0    |
| 82.5° | 4.5    |
| 85°   | 3.0    |
| 87.5° | 1.5    |



TEST NUMBER: P1247654

CATALOG NUMBER: P3AS20R359024D010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)