

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247671

Luminaire Tested: P3AS20R409024D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409024D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2087.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247671
CATALOG NUMBER: P3AS20R409024D010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1247671
 CATALOG NUMBER: P3AS20R409024D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88			88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85			85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82			82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79			79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76			76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73			73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70			70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1063796
5°	1056106
10°	1028460
15°	918711
20°	609170
25°	228207
30°	61047
35°	23851
40°	8588
45°	4093
50°	1262
55°	573
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4093 cd/sqm



TEST NUMBER: P1247671
 CATALOG NUMBER: P3AS20R409024D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.8	21.7
10°-20°	1072.3	51.4
20°-30°	486.3	23.3
30°-40°	63.0	3.0
40°-50°	10.9	0.5
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2011.3	96.4
0°-40°	2074.3	99.4
0°-60°	2086.6	100.0
0°-90°	2087.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2087.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4851	
5°	4798	453
15°	4047	1072
25°	943	486
35°	89	63
45°	13	11
55°	2	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1247671
CATALOG NUMBER: P3AS20R409024D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4851.3
1°	4848.4
2°	4841.1
3°	4830.1
4°	4816.2
5°	4797.9
6°	4776.8
7°	4750.5
8°	4718.3
9°	4674.5
10°	4618.9
11°	4553.9
12°	4467.0
13°	4359.6
14°	4219.3
15°	4046.9
16°	3827.0
17°	3576.4
18°	3275.3
19°	2957.5
20°	2610.5
21°	2263.4
22°	1921.5
23°	1581.0
24°	1246.4
25°	943.2
26°	698.5
27°	511.4
28°	384.3
29°	298.8
30°	241.1
31°	199.5
32°	166.6
32.5°	152.0
33°	137.4
34°	111.8
35°	89.1
36°	70.1
37°	55.5
37.5°	49.7
38°	43.8
39°	36.5
40°	30.0
42.5°	19.7
45°	13.2



TEST NUMBER: P1247671
CATALOG NUMBER: P3AS20R409024D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	8.0
50°	3.7
52.5°	1.5
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)